

Cuvette and Small Vessels Rinser VAKUWASCH, schuett-biotec

Cuvette and small vessels rinser VAKUWASCH

Polyethylene. Practically unbreakable. The easiest way to clean (e.g. acetone/ethanol) and to dry glass vessels in a few seconds and in one cycle. All you need is a vacuum flask (with rubber stopper with a bore hole and vacuum tube) and a low level of vacuum.

Article	Order No.
① VAKUWASCH cuvette and small vessels rinser	19 31 35001
Rubber stopper with hole	19 31 35012
Accessory for rinsing pycnometers	19 31 35014
Suction bottle DURAN®, 500 ml	19 31 35011
Vacuum tube per meter	19 31 35013

② Cuvette storage containers KÜVIBOX

For storing clean cuvettes where they are safe from dust and breakage. For cuvettes up to 55 mm high. Ready-to-hand at the point of work.

KÜVIBOX 1 for 16 cuvettes 10 mm layer depth.

KÜVIBOX 2 for 8 cuvettes 10 mm and 4 cuvettes 20 mm layer depth.

Article	Order No.
KÜVIBOX 1	29 31 82103
KÜVIBOX 2	29 31 82223

