

Sectional Stirrer Systems, neoLab®

The modular system includes a KPG® stirrer combination with an additional elastic stirrer coupling (DBGM) for flask sizes of 100 to 4000 ml.

Stirrers with KPG® shafts of various lengths and various blade forms can be combined - like the bearings - in many different ways and be adapted in modular style to the specific needs.

An elastic stirrer coupling with threaded connection ensures centered running in the KPG® stirrer bearings, reducing the risk of glass breakage.

The stirrer sleeve is made of PTFE (Teflon®). It requires no maintenance and is adjustable.

Components have standard ground joint size 29

Article

Order No.

Sectional stirrer system according to GGM

13 01 05000

