

## Magnetic Stirrers, Heidolph

### Magnetic stirrers without heating

#### Hei-Mix D / Hei-Mix L

- Top plate is insulated from the motor and protects your heat sensitive samples from any thermal damage
- To treat your sample gently and protect it from damage the rotation speed ramps up slowly until it has reached the pre – programmed speed
- Top plate diameter of 145 mm and a speed range from 100 to 1400 rpm is ideal for quantities up to 20 liter
- Hermetically sealed housing prevents corrosion and increases the service life of your unit
- You can even work with dry ice – a robust thermal insulation prevents corrosion inside the housing minimizing any dripping of condensate on the electronic components
- These models comes with a top plate material of finest quality stainless steel

#### Hei-Mix S

- Stir quick and efficiently with an extended speed range up to 2.200 rpm
- Long lasting polyamide housing and PVDF top plate material
- Ideal for titrations due to white colored top plate
- Space saving unit for efficiently mixing sample sizes up to 5 liter. Small footprint of 126 x 80 x 140 mm only, and the top plate comes with a diameter of 104 mm

| Article        | Order No.   |
|----------------|-------------|
| ① MR Hei-Mix S | 10 41 50302 |
| MR Hei-Mix L   | 10 41 50500 |
| ② MR Hei-Mix D | 10 41 50501 |



①



②