

Economy Laboratory Furnaces, Carbolite Gero

Model ELF up to 1100°C

The ceramic muffle is vacuum-formed in one piece, with heating from 2 sides to guarantee fast heating up in just approx. 30 minutes. Double skin construction with natural air circulation for low temperatures on the outer skin.

The new and fully revised design of the inner chamber includes a sturdy and wear-proof hearth. PID controller type E301 with digital display for set-point and actual temperature, plus set-point programming option.

Type	Useful H x W x D mm	Outer H x W x D mm	Vol. l	Connection	Wght kg	Order No.
① 11/6b	165x180x210	580x410x420	6.0	230 V/2 kW	24	42 71 11006
11/14b	210x220x310	630x450x520	14.0	230 V/3 kW	31	42 71 11014
11/23b	235x255x400	715x505x690	23,0	400 V/6 kW	52	10 71 11023

CARBOLITE
IGERO 35-3000 °C

